

HFM 446 *Lambda* Series

Standards	ASTM C518, ASTM C1784*, ISO 8301, JIS A1412, DIN EN 12667, DIN EN 12664*
Type	Stand-alone, with integrated printer
Air-tight system	Sample compartment with possibility to introduce purge gas
Motorized plate	Yes
Thermal conductivity range	<ul style="list-style-type: none"> ■ Up to 2.0 W/(m·K) 2.0 W/(m·K) achievable with optional instrumentation kit, recommended for hard materials and those with higher thermal conductivity ■ Accuracy: ± 1% to 2% ■ Repeatability: 0.5% ■ Reproducibility: ± 0.5% → All performance data is verified with NIST SRM 1450 D (thickness 2.5 cm)
Plate temperature range	-20°C to 90°C
Transducer metering	<ul style="list-style-type: none"> ■ <i>Small</i>: 102 mm x 102 mm ■ <i>Medium</i>: 102 mm x 102 mm ■ <i>Large</i>: 254 mm x 254 mm
Chiller system	External; constant temperature setpoint over plate temperature range
Plate temperature control	Peltier system
Plate motion	Operator-actuated plate opening for fast sample change, quick return to setpoint
Plate thermocouples	Three thermocouples on each plate, type K (two extra thermocouples with instrumentation kit)
Thermocouple resolution	± 0.01°C
Number of setpoints	Up to 10
Specimen size	<ul style="list-style-type: none"> ■ <i>Small</i>: 203 mm x 203 mm ■ <i>Medium</i>: 305 mm x 305 mm ■ <i>Large</i>: 611 mm x 611 mm
Specimen thickness (max.)	<ul style="list-style-type: none"> ■ <i>Small</i>: 51 mm ■ <i>Medium</i>: 105 mm ■ <i>Large</i>: 200 mm
Variable load/contact force	<ul style="list-style-type: none"> ■ <i>Small</i>: 0 to 854 N (21 kPa on 203 x 203 mm²) ■ <i>Medium</i>: 0 to 1930 N (21 kPa on 305 x 305 mm²) ■ <i>Large</i>: ca. 1900 N (5 kPa on 611 x 611 mm²) Precise load control and possibility to vary density of compressible materials; contact pressure calculated by software based on load sensor signal
Thickness determination	<ul style="list-style-type: none"> ■ Four-corner thickness determination via inclinometer ■ Compliance to non-parallel specimen surfaces
Software features	<ul style="list-style-type: none"> ■ <i>SmartMode</i> (incl. <i>AutoCalibration</i>, report generation, data export, wizards, user methods, predefined instrument parameters, user-defined parameters, C_p determination, etc.) ■ Storage and restoration of calibration and measurement files ■ Plot of plate/mean temperatures and thermal conductivity values ■ Monitoring of heat flux transducer signal

* not HFM 446 *Large*